

Project Name

Location

Prepared By



SATCO S12318

4.5W/LED/GY6.35/CL/830/12V

Notes

[www] 05-15-2024 04:42:54

General

Status	Active
Watts	4.5W
HID Equivalent	35W
Volts	12V
Shape	T6
Base	Bi Pin GY6.35
ANSI Base	GY6.35
Finish	Clear
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	80
Lumens	430L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	25000
Product Category	Tubular
Technology	LED

Electrical

Operating Frequency	60Hz
Dimming Type	Phase cut
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	1.85
MOD	0.71
Housing Color	Clear
Weight (lb.)	0.02

Additional Information

Installation Notes	Not for use in vapor tight fixtures.
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - Mini LED Pin Base

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes