

Project Name

Location

Prepared By



SATCO S12340

6.5W/LED/E11/FR/830/120V

Notes

[www] 05-15-2024 04:42:54

General

Status	Active
Watts	6.5W
HID Equivalent	50W
Volts	120V
Shape	T6
Base	Mini Candelabra
ANSI Base	E11
Finish	Frost
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	80+
Lumens	600L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	25000
Product Category	Tubular
Technology	LED

Electrical

Operating Frequency	60Hz
Dimming Type	Triac
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	2.83
MOD	0.75
Housing Color	Frost
Weight (lb.)	0.06

Additional Information

Installation Notes	Not for use in vapor tight fixtures.
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - Mini LED Pin Base

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes