

Project Name

Location

Prepared By



SATCO S12349

6.5W/LED/E12/FR/850/120V

Notes

[www] 05-15-2024 04:42:54

General

Status	Active
Watts	6.5W
HID Equivalent	50W
Volts	120V
Shape	T6
Base	Candelabra
ANSI Base	E12
Finish	Frost
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80+
Lumens	600L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	25000
Product Category	Tubular
Technology	LED

Electrical

Operating Frequency	60Hz
Dimming Type	Triac
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	2.91
MOD	0.75
Housing Color	Frost
Weight (lb.)	0.07

Additional Information

Installation Notes	Not for use in vapor tight fixtures.
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - Mini LED Pin Base

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
RoHS Compliant	Yes