

Project Name

Location

Prepared By



## SATCO S12355

6.5W/LED/DC/CL/850/120V

### Notes

[www] 05-15-2024 04:42:54

### General

|                  |                        |
|------------------|------------------------|
| Status           | Active                 |
| Watts            | 6.5W                   |
| HID Equivalent   | 50W                    |
| Volts            | 120V                   |
| Shape            | T6                     |
| Base             | Bayonet Double Contact |
| ANSI Base        | BA15d                  |
| Finish           | Clear                  |
| CCT (Kelvin)     | 5000K                  |
| Temperature      | Natural Light          |
| CRI              | 80+                    |
| Lumens           | 650L                   |
| Beam Spread      | 300                    |
| Dimmable         | Yes-Dimmable           |
| Hours Rated      | 25000                  |
| Product Category | Tubular                |
| Technology       | LED                    |

### Electrical

|                       |                            |
|-----------------------|----------------------------|
| Operating Frequency   | 60Hz                       |
| Dimming Type          | Triac                      |
| Operating Temperature | -20C (-4F) to +40C (+104F) |

### Physical

|               |       |
|---------------|-------|
| MOL           | 2.76  |
| MOD           | 0.75  |
| Housing Color | Clear |
| Weight (lb.)  | 0.06  |

### Additional Information

|                            |                                      |
|----------------------------|--------------------------------------|
| Installation Notes         | Not for use in vapor tight fixtures. |
| Rated For Enclosed Fixture | Yes                                  |
| Warranty                   | 3 Year Limited - Mini LED Pin Base   |

### Compliance

|                        |                               |
|------------------------|-------------------------------|
| Safety Listing         | cETLus                        |
| Location Rating        | Damp                          |
| CA T20 / T24 Rationale | Exempt - Base Not Regulated   |
| California Status      | Lawful for sale in California |
| Title 20 / 24 Status   | Lawful for sale               |
| RoHS Compliant         | Yes                           |