

Project Name

Location

Prepared By



SATCO S12358

4.5W/LED/BA15S/CL/830/12V

Notes

[www] 05-15-2024 04:42:54

General

Status	Active
Watts	4.5W
HID Equivalent	35W
Volts	12V
Shape	T6
Base	Bayonet Single Contact
ANSI Base	BA15s
Finish	Clear
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	80+
Lumens	430L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	25000
Product Category	Tubular
Technology	LED

Electrical

Operating Frequency	60Hz
Dimming Type	Triac
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	2.13
MOD	0.67
Housing Color	Clear
Weight (lb.)	0.03

Additional Information

Installation Notes	Not for use in vapor tight fixtures.
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - Mini LED Pin Base

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes