

Project Name

Location

Prepared By



# SATCO S12436

10.5A19/CL/LED/927/120V/4PK

## Notes

[www] 10-25-2021 04:00:40

### General

Status	Active
Watts	10.5W
Incandescent Equivalent	75W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700
Temperature	Warm White
CRI	90
Lumens	1100L
Beam Spread	320
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

### Electrical

Operating Frequency	60 Hz
Dimming Type	Forward Phase
Power Factor	0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

### Physical

MOL	4.02
MOD	2.36
Weight (lb.)	0.08

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 4 hr per day

### Compliance

Safety Listing	cULus Listed
Location Rating	Wet
Energy Star	Pending
California Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp