

Project Name

Location

Prepared By



SATCO S18412

13T8/U3/LED/CCT/BP/SE-DE

Notes

[www] 11-20-2023 01:02:46

General

Status	Active
Watts	13W
Incandescent Equivalent	50W
Fluorescent Equivalent	32W
Volts	120V-277V
Ballast Type	Type B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	22.5
Finish	White
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Neutral White to Natural Light
CRI	80
Lumens	1850L/1950L/1950L
Beam Spread	160
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	U-Bend
Technology	LED

Electrical

Ballasting Requirements	Ballast Bypass
Operating Frequency	50/60Hz
Power Factor	0.9
THD	20%
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	22.6
MOD	1
Leg Spacing	3
Material	Plastic
Lens Finish	Frost
Lens Material	Plastic
Housing Color	White

Additional Information

Additional Info	Replaces FB34T12/U3
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - T8 LED Bulbs

Compliance

Safety Listing	cRUus - Recognized Component; ETLus - Listed; cULus - Classified
Location Rating	Damp
Energy Star	No
DLC Approved	No
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes

NSF Approved	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
<http://www.satco.com/>

