

Project Name

Location

Prepared By



Notes

[www] 05-15-2024 04:42:54

General

Status	Active
Watts	11W
Incandescent Equivalent	50W
Fluorescent Equivalent	24W
Volts	120V-277V
Ballast Type	Type A
Shape	T5
Base	Miniature Bi Pin
ANSI Base	G5
Nominal Length	24
Finish	White
CCT (Kelvin)	3500K
Temperature	Neutral White
CRI	82
Lumens	1350L
Beam Spread	185
Dimmable	Yes-Dimmable
Hours Rated	50000
Product Category	Type A
Technology	LED

Electrical

Ballasting Requirements	Ballast required
Operating Frequency	50/60Hz
Dimming Note	Only in Type A mode; Check Ballast MFG for Dimmer Compatibility
Power Factor	0.9
THD	20%
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	22.5
MOD	0.63
Material	Aluminum / Glass
Lens Material	Glass
Weight (lb.)	0.13

Additional Information

Additional Info	Light Emitting Area of 325 degrees; System Wattage (Type A) - 14W
Installation Notes	Not for use in vapor tight fixtures.
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - T5 LED Bulbs

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	No
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California

Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes
SDS Sheet	LED_Lamp

