

Project Name

Location

Prepared By



SATCO S21236

6G25/LED/CL/940/120V

Notes

[www] 07-11-2022 03:01:10

General

Status	Active
Watts	6W
Incandescent Equivalent	60W
Volts	120V
Shape	G25
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	4000K
Temperature	Cool White
CRI	90
Lumens	500L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	15000
Technology	LED

Electrical

Operating Frequency	60 Hz
Power Factor	>0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.45
MOD	3.15
Weight (lb.)	0.088

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Pending
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes