

Project Name

Location

Prepared By



SATCO S21414

18W/PL/LED/HL/5CCT/G24

Notes

[www] 01-15-2024 02:40:00

General

Status	Active
Watts	18W
Fluorescent Equivalent	32W
Volts	120V/277V
Ballast Type	Type B
Shape	PL
Base	G24d (2-Pin)
ANSI Base	G24d
Finish	White
CCT (Kelvin)	3000K/3500K/4000K/5000K/6500K
Temperature	Warm White to Natural Light
CRI	82
Lumens	2250L-2340L
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	PL 2-Pin
Operating Position	Universal
Technology	LED

Electrical

Operating Frequency	50/60Hz
Power Factor	>0.9
THD	20%
Operating Temperature	-25C (-13F) to +50C (+122F)

Physical

MOL	6.12
MOD	1.95
Weight (lb.)	0.42

Additional Information

Installation Notes	Suggested wattage equivalency = 32W CFL
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus - Listed; cULus - Classified
Location Rating	Damp
Energy Star	No
DLC Approved	No
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
SDS Sheet	LED_Lamp