

Project Name

Location

Prepared By



SATCO S21745

5.5MR16/LED/40°/850/GU10/2PK

Notes

[www] 01-15-2024 02:40:10

General

Status	Active
Watts	5.5W
Incandescent Equivalent	50W
Volts	120V
Shape	MR16
Base	Bi Pin GU10
ANSI Base	GU10
Finish	White
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80
Lumens	500L
Beam Spread	40
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	MR
Technology	LED

Electrical

Operating Frequency	60Hz
CBCP	750
Power Factor	0.7
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	2.2
MOD	1.97
Lensed	Lensed Lamp
Lens Finish	Clear
Housing Color	White
Weight (lb.)	0.09

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp