

Project Name

Location

Prepared By



# SATCO S21861

4T6.5/LED/CL/930/120V/DC/1CD

## Notes

[www] 05-17-2020 02:53:17

### General

Status	Active
Watts	4W
Incandescent Equivalent	40W
Volts	120V
Shape	T6.5
Base	Bayonet Double Contact
ANSI Base	BA15d
Finish	Clear
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	90
Lumens	400L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Tubular
Technology	LED

### Electrical

Dimming Note	120V only
Power Factor	0.76
Operating Temperature	-20C (-4F) to +45C (+113F)

### Physical

MOL	5.00
MOD	0.79
Weight (lb.)	0.044

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

### Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	No
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes