

Project Name

Location

Prepared By



SATCO S21864

5.5T10/LED/FR/930/120V/E26/2CD

Notes

[www] 05-17-2020 02:53:17

General

Status	Active
Watts	5.5W
Incandescent Equivalent	40W
Volts	120V
Shape	T10
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	90
Lumens	450L
Beam Spread	320
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Tubular
Technology	LED

Electrical

Dimming Note	120V only
Power Factor	0.75
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	5.00
MOD	1.25
Weight (lb.)	0.123

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes