

Project Name

Location

Prepared By



## SATCO S21868

8T9/LED/FR/927/120V/E26/2CD

### Notes

[www] 05-17-2020 02:53:17

### General

Status	Active
Watts	8W
Incandescent Equivalent	75W
Volts	120V
Shape	T9
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	90
Lumens	700L
Beam Spread	320
Dimmable	Yes-Dimmable
Hours Rated	15000
Technology	LED

### Electrical

Dimming Note	120V only
Power Factor	0.78
Operating Temperature	-20C (-4F) to +45C (+113F)

### Physical

MOL	7.20
MOD	1.18
Weight (lb.)	0.176

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

### Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes