

Project Name

Location

Prepared By



SATCO S21885

4CA10/LED/950/CL/120V/E26/2CD

Notes

(www) 06-12-2024 03:11:04

General

| | |
|-------------------------|---------------|
| Status | Active |
| Watts | 4W |
| Incandescent Equivalent | 40W |
| Volts | 120V |
| Shape | CA10 |
| Base | Medium |
| ANSI Base | E26 |
| Finish | Clear |
| CCT (Kelvin) | 5000K |
| Temperature | Natural Light |
| CRI | 90 |
| Lumens | 350L |
| Beam Spread | 300 |
| Dimmable | Yes-Dimmable |
| Dimming Note | 120V only |
| Hours Rated | 15000 |
| Product Category | Candle |
| Technology | LED |

Smart Product Info

| | |
|-------------|----|
| IOT Enabled | No |
|-------------|----|

Electrical

| | |
|-----------------------|----------------------------|
| Operating Frequency | 60Hz |
| Power Factor | 0.75 |
| Operating Position | Universal |
| Operating Temperature | -20C (-4F) to +45C (+113F) |

Physical

| | |
|--------------|------|
| MOL | 4.33 |
| MOD | 1.38 |
| Weight (lb.) | 0.07 |

Additional Information

| | |
|----------------------------|----------------|
| Rated For Enclosed Fixture | Yes |
| Warranty | 3 Year Limited |

Compliance

| | |
|------------------------|-------------------------------|
| Safety Listing | cETLus - Listed |
| Location Rating | Wet |
| Energy Star | Yes |
| ES Unique ID | ESID-2884628 |
| UL Application | Filament LED Lamp |
| CA T20 / T24 Rationale | T20 Listed |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | Lawful for sale |
| RoHS Compliant | Yes |