

Project Name

Location

Prepared By



SATCO S21886

4CA10/LED/950/FR/120V/E26/2CD

Notes

(www) 06-12-2024 03:11:34

General

Status	Active
Watts	4W
Incandescent Equivalent	40W
Volts	120V
Shape	CA10
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	90
Lumens	350L
Beam Spread	300
Dimmable	Yes-Dimmable
Dimming Note	120V only
Hours Rated	15000
Product Category	Candle
Technology	LED

Smart Product Info

IOT Enabled	No
-------------	----

Electrical

Operating Frequency	60Hz
Power Factor	0.76
Operating Position	Universal
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	4.33
MOD	1.38
Weight (lb.)	0.07

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2883626
UL Application	Filament LED Lamp
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes