

Project Name

Location

Prepared By



IMAGE NOT AVAILABLE

## SATCO S23152

36W/LED/CCT/100-277V/EX39

### Notes

[www] 04-25-2022 02:43:09

### General

Status	Active
Watts	36W/27W/18W
HID Equivalent	150W/125W/75W
Volts	100V-277V
Base	Extended Mogul
ANSI Base	EX39
Finish	White
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Warm to Cool White
CRI	80
Lumens	5040L/3780L/2520L
Beam Spread	360
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Corncob
Technology	LED
Ballasting Requirements	Ballast Bypass

### Electrical

Operating Frequency	50-60 Hz
Dimming Note	Dimmable only via the wattage/lumen selectable dial included on lamp
Power Factor	>0.9
Burning Position	Base Up, Base Down, or Horizontal
Surge Protection	Built-in surge protection - 4KV
Operating Temperature	-30C (-22F) to a maximum of +45C (+113F)

### Physical

MOL	8.50
MOD	3.35
Lens Material	Plastic
Housing Color	Dark Gray
Weight (lb.)	1.47

### Additional Information

Additional Info	Power selectable
IP Rating	IP64
Warranty	5 Year Limited - 12 hr per day

### Compliance

Safety Listing	cULus - Classified; cULus - Certified; cULus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	S-6CIPQ4
CA T20 / T24 Rationale	Exempt - Base Not Regulated
RoHS Compliant	Yes
FCC Compliant	Yes

