Project Name

Location | Prepared By



SATCO S28932

80W/LED/HID/SB/5K/EX39

Notes

[www] 10-26-2020 00:08:09

General

Status	Active
Watts	80
Incandescent Equivalent	400
HID Equivalent	250
Volts	100V-277V
Shape	Corncob
Base	Mogul Extended
ANSI Base	EX39
Finish	White
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	83
Lumens	10400
Beam Spread	180
Dimmable	Dimmable with optional control modules
Hours Rated	50000
Lamp Type	Shoebox
Technology	LED
Min Compartment Size	Length: 11 in. Width: 9.2 in. Height: 11 in.

Electrical

Operating Frequency	50/60 Hz
Dimming Type	Step & Stepless dimming
Power Factor	0.9
Surge Protection	Built-in surge protection - 4KV
Operating Temperature	-30C (-22F) to a maximum of +45C (+113F)

Physical

MOL	8.77
MOD	4.38
Housing Color	White
Weight (lb.)	2.42

Additional Information

Rated For Enclosed Fixture	Yes
IP Rating	IP64
Specification Note	This is not to be used with a ballast
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PL0NRCV506NZ
CEC Status	Lawful for sale in California
RoHS Compliant	Yes

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
https://www.satco.com/

FCC Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc.
All Rights Reserved