

Project Name

Location

Prepared By



SATCO S28937

110W/LED/HID/SB/3K/EX39

Notes

[www] 10-26-2020 00:00:00

General

Status	Active
Watts	110
Incandescent Equivalent	750
HID Equivalent	400
Volts	100V-277V
Shape	Comcob
Base	Mogul Extended
ANSI Base	EX39
Finish	White
CCT (Kelvin)	3000
Temperature	Warm White
CRI	83
Lumens	14300
Beam Spread	180
Dimmable	Dimmable with optional control modules
Hours Rated	50000
Lamp Type	Shoebox
Technology	LED
Min Compartment Size	Length: 11 in. Width: 11.6 in. Height: 11 in.

Electrical

Operating Frequency	50/60 Hz
Dimming Type	Step & Stepless dimming
Power Factor	0.9
Surge Protection	Built-in surge protection - 4KV
Operating Temperature	-30C (-22F) to a maximum of +45C (+113F)

Physical

MOL	11.13
MOD	4.38
Housing Color	White
Weight (lb.)	3.67

Additional Information

Rated For Enclosed Fixture	Yes
IP Rating	IP64
Specification Note	This is not to be used with a ballast
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLE2XRXMJUC
CEC Status	Lawful for sale in California
RoHS Compliant	Yes

FCC Compliant

Yes

SDS Sheet

LED_Lamp

