

Project Name

Location

Prepared By



SATCO S28976

50-FT/LED/5PC/TEMP/STRING/120V

Notes

[www] 09-21-2020 03:40:10

General

Status	Active
Watts	50
HID Equivalent	200
Volts	120V
Shape	Comcob
Base	Plug - 2 Prong
ANSI Base	Plug
Finish	Orange
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	6000
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Work Light
Technology	LED

Electrical

Operating Frequency	60 Hz
Power Factor	0.9
Operating Temperature	-30C (-22F) to a maximum of +45C (+113F)

Physical

MOL	5.3
MOD	3.7
Lens Finish	Frosted
Lens Material	Plastic
Housing Color	Orange/White
Photocell	No
Weight (lb.)	3.96

Additional Information

Additional Info	A single set is 50 feet in length; Linkable up to 10 sets
Enclosure Rating	Open Rated Lamp
Rated For Enclosed Fixture	No
IP Rating	IP65
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

