

Project Name

Location

Prepared By



# SATCO S2926

F40T12/368BL

## Notes

[www] 03-15-2021 00:27:52

### General

Status	Active
Watts	40
Shape	T12
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48
Finish	White
Beam Spread	360
Hours Rated	20000
Lamp Type	Linear
Technology	Fluorescent

### Electrical

Operating Temperature	Ballast Dependent
-----------------------	-------------------

### Physical

MOL	47.78
MOD	1.5
Weight (lb.)	.002

### Additional Information

Warranty	Avg. Rated Hour Limited
----------	-------------------------

### Compliance

Energy Star	No
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	Black_Light_Fluorescent_Lamp