

Project Name

Location

Prepared By



SATCO S32250

21PAR38/5CCT/HL/120V/D

Notes

(www) 06-12-2024 03:11:05

General

Status	Active
Watts	21W
Incandescent Equivalent	250W
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	Silver
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Temperature	Warm White to Natural Light
CRI	90
Lumens	3000L
Beam Spread	40
Dimmable	Yes-Dimmable
Dimming Note	120V Only
Hours Rated	25000
Product Category	PAR
Technology	LED

Electrical

Operating Frequency	60Hz
CBCP	3272
Power Factor	0.9
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	5.12
MOD	4.76
Lensed	Lensed Lamp
Lens Finish	Frost
Lens Material	Polycarbonate (PC)
Housing Color	Silver
Weight (lb.)	0.4

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 12 hr per day

Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed; T20 Exempt - >2600 Lumens
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp