

Project Name

Location

Prepared By



## SATCO S33112

100W/LED/HID-HB/4K/100-277V

### Notes

[www] 11-26-2022 02:03:00

### General

Status	Active
Watts	60W/80W/100W
HID Equivalent	175W/250W/320W
Volts	100V-277V
Shape	Hi-Bay
Base	Mogul Extended
ANSI Base	EX39
Finish	White
CCT (Kelvin)	4000K
Temperature	Cool White
CRI	80
Lumens	8400L/11220L/14000L
Beam Spread	120
Dimmable	Non-Dimmable
Hours Rated	50000
Technology	LED
Min Compartment Size	Length: 15.75 in. Width: 14.96 in.
Ballasting Requirements	Ballast Bypass

### Electrical

Operating Frequency	50/60 Hz
Surge Protection	Built-in surge protection - 4KV
Operating Temperature	-25C (-13F) to +50C (+122F)

### Physical

MOL	9.13
MOD	5.51
Weight (lb.)	2.68

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - Hi-Pro

### Compliance

Safety Listing	cULus - Listed; cULus - Classified
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp