

Project Name

Location

Prepared By



## SATCO S33115

130W/LED/HID-HB/5K/100-277V

### Notes

[www] 11-26-2022 02:03:09

### General

|                         |                                    |
|-------------------------|------------------------------------|
| Status                  | Active                             |
| Watts                   | 80W/100W/130W                      |
| HID Equivalent          | 250W/320W/400W                     |
| Volts                   | 100V-277V                          |
| Shape                   | Hi-Bay                             |
| Base                    | Mogul Extended                     |
| ANSI Base               | EX39                               |
| Finish                  | White                              |
| CCT (Kelvin)            | 5000K                              |
| Temperature             | Natural Light                      |
| CRI                     | 80                                 |
| Lumens                  | 11200L/14000L/18200L               |
| Beam Spread             | 120                                |
| Dimmable                | Non-Dimmable                       |
| Hours Rated             | 50000                              |
| Technology              | LED                                |
| Min Compartment Size    | Length: 15.75 in. Width: 14.96 in. |
| Ballasting Requirements | Ballast Bypass                     |

### Electrical

|                       |                                 |
|-----------------------|---------------------------------|
| Operating Frequency   | 50/60 Hz                        |
| Surge Protection      | Built-in surge protection - 4KV |
| Operating Temperature | -25C (-13F) to +50C (+122F)     |

### Physical

|              |      |
|--------------|------|
| MOL          | 9.72 |
| MOD          | 5.51 |
| Weight (lb.) | 2.70 |

### Additional Information

|                            |                         |
|----------------------------|-------------------------|
| Rated For Enclosed Fixture | Yes                     |
| Warranty                   | 5 Year Limited - Hi-Pro |

### Compliance

|                        |                                    |
|------------------------|------------------------------------|
| Safety Listing         | cULus - Listed; cULus - Classified |
| Location Rating        | Damp                               |
| Energy Star            | No                                 |
| CA T20 / T24 Rationale | Exempt - Base Not Regulated        |
| California Status      | Lawful for sale in California      |
| Title 20 / 24 Status   | Lawful for sale                    |
| RoHS Compliant         | Yes                                |
| FCC Compliant          | Yes                                |
| SDS Sheet              | LED_Lamp                           |