

Project Name

Location

Prepared By



Notes

[www] 03-09-2021 01:43:27

General

| | |
|-------------------------|---------------|
| Status | Active |
| Watts | 9.5 |
| Incandescent Equivalent | 60 |
| Fluorescent Equivalent | 13 |
| Volts | 120V |
| Shape | A19 |
| Base | Medium |
| ANSI Base | E26 |
| Finish | Frosted |
| CCT (Kelvin) | 5000 |
| Temperature | Natural Light |
| CRI | 80 |
| Lumens | 800 |
| Beam Spread | 220 |
| Dimmable | Non-Dimmable |
| Hours Rated | 15000 |
| Lamp Type | Type A |
| Technology | LED |

Electrical

| | |
|-----------------------|--|
| Power Factor | 0.6 |
| Operating Temperature | -25C (-13F) to a maximum of 45C (113F) |

Physical

| | |
|---------------|-------|
| MOL | 4.33 |
| MOD | 2.36 |
| Housing Color | White |
| Weight (lb.) | 0.09 |

Additional Information

| | |
|----------------------------|--------------------------------|
| Rated For Enclosed Fixture | Yes |
| Warranty | 3 Year Limited - 10 hr per day |

Compliance

| | |
|-------------------|---------------|
| Safety Listing | cULus Listed |
| Location Rating | Damp |
| Energy Star | Yes |
| ES Unique ID | ESID-2370420 |
| California Status | Non-Compliant |
| RoHS Compliant | Yes |
| SDS Sheet | LED_Lamp |