

Project Name

Location

Prepared By



SATCO S6409

F40T12 BLB BLACKLIGHT BLUE

Notes

[www] 03-22-2021 04:50:57

General

Status	Active
Watts	40
Shape	T12
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48
Finish	Blue
Beam Spread	360
Hours Rated	20000
Lamp Type	Linear
Technology	Fluorescent

Electrical

Operating Temperature	Ballast Dependent
-----------------------	-------------------

Physical

MOL	47.78
MOD	1.5
Housing Color	None
Weight (lb.)	0.0049

Additional Information

Additional Info	Peak 368 nm.
Warranty	Avg. Rated Hour Limited

Compliance

Energy Star	No
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	Black_Light_Fluorescent_Lamp