

Project Name

Location

Prepared By



## SATCO S8051

1W/LED/S14/TW/FR/12V/2PK

### Notes

[www] 01-15-2024 02:40:13

### General

Status	Active
Watts	1W
Incandescent Equivalent	11W
Volts	12V
Shape	S14
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	2700K-5000K
Temperature	Tunable White
CRI	80
Lumens	100L
Beam Spread	300
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App
Hours Rated	15000
Lamp Type	String Light
Technology	LED

### Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Alexa; Google Home; Siri; SmartThings

### Electrical

Power Factor	>0.8
Operating Temperature	-20C (-4F) to +45C (+113F)

### Physical

MOL	3.35
MOD	1.78
Weight (lb.)	0.03

### Additional Information

Rated For Enclosed Fixture	No
Warranty	3 Year Limited

### Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
RoHS Compliant	Yes