

Project Name

Location

Prepared By



SATCO S8052

2W/LED/G25/822/120V/2PK

Notes

[www] 01-15-2024 02:40:12

General

Status	Active
Watts	2W
Incandescent Equivalent	15W
Volts	120V
Shape	G25
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2200K
CRI	80
Lumens	80L
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	15000
Lamp Type	String Light
Technology	LED

Smart Product Info

IOT Enabled	No
-------------	----

Electrical

Operating Frequency	60Hz
Power Factor	>0.8
Operating Temperature	-20C (-4F) to +60C (+140F)

Physical

MOL	4.92
MOD	3.12
Weight (lb.)	0.04

Additional Information

Rated For Enclosed Fixture	No
Warranty	3 Year Limited

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
RoHS Compliant	Yes