

Project Name

Location

Prepared By



## NUVO TH487

24W LED SQUARE DUAL TRACK HEAD

### Notes

[www] 10-05-2020 02:05:57

### General

Status	Active
Type	Track Head
Wattage	24
Finish	White
Beam Angle	36
CCT (Kelvin)	3000
Temperature	Warm White
Indoor or Outdoor Fixture	Indoor

### Specifications

CRI	90
Lumen Output	2040
Rated Hours	30000
Voltage	120V
Dimmable	Yes - Dimmable
Compatible Dimmers	Triac
Weight (lb.)	1.74

### Dimensions

Height (in.)	6.00
Width (in.)	2.25
Length (in.)	6.75

### Compliance

Safety Listing	cETLus
Location Rating	Dry
UL Application	Ceiling
Energy Star	No
CEC Status	Lawful for sale in California
CA Prop 65	Lead
RoHS Compliant	Yes

### Additional Information

Warranty	3 Year Limited - Fixtures
----------	---------------------------