

W-SERIES DIRECT HEAT

TABLETOP SEALERS

sealersales



Seals thicker materials like coffee bags

- Easy to operate
- Protector bars around sealing jaws
- Seals a variety of thermoplastic materials
- German manufactured temperature controller
- PTFE coated jaws
- Seal length: 12" (300mm)
- Seal width: 3/5" (15mm)
- Seal style: meshed ++ or serrated ==



Introducing our top-of-the-line **W-Series W-300DAT(S) Tabletop Direct Heat Sealers**, designed to seal a wide range of thermoplastic materials with precision and efficiency. These sealers handle various materials, including coated aluminum foil, Kraft paper, cellophane, polypropylene, poly-nylon, and even thicker options. Please note that while these sealers can tackle a multitude of materials, they are not suitable for sealing polyethylene.

With the capacity to seal materials up to 12 inches in width and 20 mils in total thickness, our W-Series sealers boast a German-manufactured thermostat, ensuring precise temperature control from 30° to 550° F (0° to 300° C). The unit is also equipped with an electronic timer to adjust seal time and ensure consistent seals every time. Choose from two models: W-300DAT comes equipped with meshed (++) seal bars, while the W-300DATS comes equipped with serrated (=) seal bars.

Operating our W-Series sealers is simple! Simply set the desired temperature on the temperature controller based on your material's requirements. Set the timer for length of seal time. Just insert the material between the two sealing bars, press down on the footswitch to activate sealing.

SPECIFICATIONS	W-300DAT	W-300DATS
POWER	110V / 50HZ / 350W	110V / 50HZ / 350W
SEAL LENGTH	12" (300MM)	12" (300MM)
SEAL WIDTH	15MM (3/5")	15MM (3/5")
SEAL STYLE	MESHED ++	SERRATED ==
TEMPERATURE RANGE	30° to 550° F (0° to 300° C)	30° to 550° F (0° to 300° C)
WEIGHT	38-LBS	38-LBS
DIMENSIONS	13" X 14" X 7"	13" X 14" X 7"



Meshed Seal Style

Serrated Seal Style

