



LED 4FT Multi Wattage Multi CCT Vapor Tight High Bay Light

CONSTRUCTION:

PC housing and white cover with stainless steel clips.

OPTICAL SYSTEM:

Lumiled 2835 LED chips. 110° beam angle.

WARRANTY:

5-year limited warranty. Actual performance may differ as a result of end-user environment and application.

ELECTRICAL:

120-277V input standard.
-20°C to 40°C, -4°F to 104°F

INSTALLATION & MOUNTING:

Surface mount or suspension mount.

CONTROLS & DIMMING:

0-10V dimming comes standard. Suitable for use with LED dimmers. Auxiliary 12V output.

FEATURES

- Default Wattage:
 - 4FT – 90W
 - 4FT – 180W
- Default CCT: 5,000K
- IK10 & IP65 rating
- Dust-tight
- NSF rated for splash zone and nonfood zone
- Auxiliary 12V output
- Linkable design (see page 2 for details)
- 100,000 hours lifetime

SUITABLE APPLICATIONS

- Food / beverage factories
- Heavy manufacturing facilities
- Underground parking
- Refrigerated storage room
- Warehouse
- Tunnel

4FT
60W, 75W and 90W

or

4FT
120W, 150W and 180W



MOUNTING OPTIONS:



Surface Mount



Suspension Kit
(Not included)

DLC Product ID:

- LOC-4FTVTHB-MW(60/75/90)MCCT(35/40/50) – PLU6GA9WADCZ
- LOC-4FTVTHB-MW(120/150/180)MCCT(35/40/50) – PLN3R7YZ81ML

OPTIONAL ACCESSORIES:



Emergency Back-up



Sensor



Remote Control
LOC-RC-100



LOC-4FTVTHB-MW(60/75/90)MCCT(35/40/50)

WATTAGE SELECTABLE	CCT SELECTABLE	LUMENS	EFFICACY	VOLTAGE	CRI	POWER FACTOR	THD	REPLACES
60W	3500K / 4000K / 5000K	8,916LM	148.6lm/W	120-277V	80	0.9	20%	4 32W LED tube
75W	3500K / 4000K / 5000K	11,145LM	148.6lm/W	120-277V	80	0.9	20%	4 32W LED tube
90W	3500K / 4000K / 5000K	13,374LM	148.6lm/W	120-277V	80	0.9	20%	4 32W LED tube

LOC-4FTVTHB-MW(120/150/180)MCCT(35/40/50)

WATTAGE SELECTABLE	CCT SELECTABLE	LUMENS	EFFICACY	VOLTAGE	CRI	POWER FACTOR	THD	REPLACES
120W	3500K / 4000K / 5000K	17,772LM	148.1lm/W	120-277V	80	0.9	20%	250W MH
150W	3500K / 4000K / 5000K	22,215LM	148.1lm/W	120-277V	80	0.9	20%	250W MH
180W	3500K / 4000K / 5000K	26,658LM	148.1lm/W	120-277V	80	0.9	20%	250W MH

LINKING TOGETHER

Model Number	Voltage (18AWG)	Linkable Qty	Voltage (16AWG)	Linkable Qty
LOC-4FTVTHB-MW(60/75/90)MCCT(35/40/50)	120V	10	120V	15
	240V	20	240V	30
	277V	24	277V	35
LOC-4FTVTHB-MW(120/150/180)MCCT(35/40/50)	120V	5	120V	8
	240V	10	240V	16
	277V	12	277V	18

MEASUREMENTS



MODEL	QUANTITY	WEIGHT	UPC CODE
LOC-4FTVTHB-MW(60/75/90)MCCT(35/40/50)	1	lbs	00815586029686
LOC-4FTVTHB-MW(120/150/180)MCCT(35/40/50)	1	lbs	00810050940351