



One Piece Mesh Body of
2 Mesh x .063" Welded Wire
(.437" Openings, 76% Open Area)

| | |
|---------------------------------|---------------------|
| UNLESS OTHERWISE SPECIFIED: | |
| DIMENSIONS ARE IN INCHES | |
| TOLERANCES: | |
| FRACTIONAL $\pm 1/16$ " | |
| ANGULAR: ± 5 DEG. | |
| TWO PLACE DECIMAL ± 0.03 | |
| THREE PLACE DECIMAL ± 0.015 | |
| EST WGT | 0.4 lbs. |
| MATERIAL | 304 Stainless Steel |
| FINISH | Natural |
| DO NOT SCALE DRAWING | |

Light Duty Mesh Basket: 6Lx6Wx1H,
304 SS, No Handles, Mesh: 2 x .063

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
THREE M TOOL. ANY REPRODUCTION IN
PART OR AS A WHOLE WITHOUT THE
WRITTEN PERMISSION OF THREE M TOOL
IS PROHIBITED.

SIZE **B** DWG. NO.
FLB-060060010-N02S

SCALE: 1:3

SHEET 1 OF 1