



One Piece Mesh Body of
2 Mesh x .063" Welded Wire
(.437" Openings, 76% Open Area)

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL ± 1/16"
ANGULAR: ± 5 DEG.
TWO PLACE DECIMAL ±0.03
THREE PLACE DECIMAL ±0.015

Light Duty Mesh Basket: 6Lx6Wx3H,
304 SS, No Handles, Mesh: 2 x .063

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
THREE M TOOL. ANY REPRODUCTION IN
PART OR AS A WHOLE WITHOUT THE
WRITTEN PERMISSION OF THREE M TOOL
IS PROHIBITED.

EST WGT

0.6 lbs.

MATERIAL
304 Stainless Steel

FINISH
Natural

SIZE
B

DWG. NO.
FLB-060060030-N02S

DO NOT SCALE DRAWING

SCALE: 1:3

SHEET 1 OF 1