



Lined Bottom and Sides with  
30 Mesh x .012" Woven Wire  
(.021" Openings, 40% Open Area)

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL ± 1/16"  
ANGULAR: ± 5 DEG.  
TWO PLACE DECIMAL ±0.03  
THREE PLACE DECIMAL ±0.015

**Rectangular Wire Mesh Basket:**  
4Lx4Wx3H, 304 SS, 3/16 Rod Frame,  
No Handles, Mesh: 30 x .012

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS  
DRAWING IS THE SOLE PROPERTY OF  
THREE M TOOL. ANY REPRODUCTION IN  
PART OR AS A WHOLE WITHOUT THE  
WRITTEN PERMISSION OF THREE M TOOL  
IS PROHIBITED.

EST WGT  
0.6 lbs.  
MATERIAL  
304 Stainless Steel  
FINISH  
Natural  
DO NOT SCALE DRAWING

SIZE **B** DWG. NO.  
TMT-040040030-N30S

SCALE: 1:2

SHEET 1 OF 1