



Lined Bottom and Sides with  
4 Mesh x .063" Woven Wire  
(.187" Openings, 56% Open Area)

**PROPRIETARY AND CONFIDENTIAL**

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL  $\pm 1/16"$   
ANGULAR:  $\pm 5$  DEG.  
TWO PLACE DECIMAL  $\pm 0.03$   
THREE PLACE DECIMAL  $\pm 0.015$

EST WGT  
2.0 lbs.  
MATERIAL  
304 Stainless Steel  
FINISH  
Natural

DO NOT SCALE DRAWING

**Rectangular Wire Mesh Basket:  
6Lx6Wx4H, 304 SS, 3/16 Rod Frame,  
Stacking Handles, Mesh: 4 x .063**

SIZE **B** DWG. NO.  
TMT-060060040-A04S

SCALE: 1:3

SHEET 1 OF 1