



Lined Bottom and Sides with
4 Mesh x .063" Woven Wire
(.187" Openings, 56% Open Area)

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL ± 1/16"
ANGULAR: ± 5 DEG.
TWO PLACE DECIMAL ±0.03
THREE PLACE DECIMAL ±0.015

EST WGT
3.2 lbs.
MATERIAL
304 Stainless Steel
FINISH
Natural

Rectangular Wire Mesh Basket:
10Lx6Wx6H, 304 SS, 3/16 Rod Frame,
Stacking Handles, Mesh: 4 x .063

SIZE **B** DWG. NO.
TMT-100060060-A04S

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
THREE M TOOL. ANY REPRODUCTION IN
PART OR AS A WHOLE WITHOUT THE
WRITTEN PERMISSION OF THREE M TOOL
IS PROHIBITED.

DO NOT SCALE DRAWING

SCALE: 1:4

SHEET 1 OF 1