



Lined Bottom and Sides with  
8 Mesh x .047" Woven Wire  
(.078" Openings, 39% Open Area)

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL ± 1/16"  
ANGULAR: ± 5 DEG.  
TWO PLACE DECIMAL ±0.03  
THREE PLACE DECIMAL ±0.015

EST WGT  
3.1 lbs.  
MATERIAL  
304 Stainless Steel  
FINISH  
Natural

**Rectangular Wire Mesh Basket:**  
10Lx6Wx6H, 304 SS, 3/16 Rod  
Frame, No Handles, Mesh: 8 x .047

SIZE **B** DWG. NO.  
TMT-100060060-N08S

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS  
DRAWING IS THE SOLE PROPERTY OF  
THREE M TOOL. ANY REPRODUCTION IN  
PART OR AS A WHOLE WITHOUT THE  
WRITTEN PERMISSION OF THREE M TOOL  
IS PROHIBITED.

DO NOT SCALE DRAWING

SCALE: 1:4

SHEET 1 OF 1