



Line Bottom, Sides, and Lid with  
2 Mesh x .063" Welded Wire  
(.437" Openings, 76% Open Area)

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL  $\pm 1/16$ "  
ANGULAR:  $\pm 5$  DEG.  
TWO PLACE DECIMAL  $\pm 0.03$   
THREE PLACE DECIMAL  $\pm 0.015$

**Rectangular Wire Mesh Basket:**  
10Lx6Wx6H, 304 SS, 3/16 Rod Frame,  
Hinged Lid with Latch, Mesh: 2 x .063

**PROPRIETARY AND CONFIDENTIAL**

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

EST WGT  
2.6 lbs.  
MATERIAL  
304 STAINLESS STEEL  
FINISH  
NATURAL

SIZE **B** DWG. NO.  
TMT-100060060-P02S

DO NOT SCALE DRAWING

SCALE: 1:4

SHEET 1 OF 1