



Lined Bottom and Sides with  
2 Mesh x .063" Welded Wire  
(.437" Openings, 76% Open Area)

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED:		<b>Rectangular Wire Mesh Basket:</b> 10Lx10Wx10H, 304 SS, 3/16 Rod Frame, Stacking Handles, Mesh: 2 x .063	
DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/16" ANGULAR: ± 5 DEG. TWO PLACE DECIMAL ±0.03 THREE PLACE DECIMAL ±0.015			
EST WGT	3.8 lbs.		
MATERIAL	304 Stainless Steel	SIZE	DWG. NO.
FINISH	Natural	<b>B</b>	TMT-100100100-A02S
DO NOT SCALE DRAWING		SCALE: 1:5	
		SHEET 1 OF 1	