



$\phi \frac{3}{16}"$
Rod Frame



Lined Bottom and Sides with
4 Mesh x .063" Woven Wire
(.187" Openings, 56% Open Area)



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL $\pm 1/16"$
ANGULAR: ± 5 DEG.
TWO PLACE DECIMAL ± 0.03
THREE PLACE DECIMAL ± 0.015

EST WGT
4.5 lbs.
MATERIAL
304 Stainless Steel
FINISH
Natural

Round Wire Mesh Basket: 10Dia. x 12H,
304 SS, 3/16 Rod Frame, Swinging Round
Loop Handle Mesh: 4 x .063

SIZE **B** DWG. NO.
TMT-100RND120-C04S

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
THREE M TOOL. ANY REPRODUCTION IN
PART OR AS A WHOLE WITHOUT THE
WRITTEN PERMISSION OF THREE M TOOL
IS PROHIBITED.

DO NOT SCALE DRAWING

SCALE: 1:5

SHEET 1 OF 1