



$\phi \frac{3}{16}$ "  
Rod Frame



Lined Bottom and Sides with  
30 Mesh x .012" Woven Wire  
(.021" Openings, 40% Open Area)



UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL  $\pm 1/16$ "  
ANGULAR:  $\pm 5$  DEG.  
TWO PLACE DECIMAL  $\pm 0.03$   
THREE PLACE DECIMAL  $\pm 0.015$

Round Wire Mesh Basket: 10Dia. x 12H,  
304 SS, 3/16 Rod Frame, Swinging Round  
Loop Handle, Mesh: 30 x .012

**PROPRIETARY AND CONFIDENTIAL**

THE INFORMATION CONTAINED IN THIS  
DRAWING IS THE SOLE PROPERTY OF  
THREE M TOOL. ANY REPRODUCTION IN  
PART OR AS A WHOLE WITHOUT THE  
WRITTEN PERMISSION OF THREE M TOOL  
IS PROHIBITED.

EST WGT  
2.3 lbs.

MATERIAL  
304 Stainless Steel

FINISH  
Natural

SIZE **B** DWG. NO.  
TMT-100RND120-C30S

DO NOT SCALE DRAWING

SCALE: 1:5

SHEET 1 OF 1