


$\phi \frac{3}{16}$ "  
Rod Frame



Lined Bottom and Sides with  
8 Mesh x .047" Woven Wire  
(.078" Openings, 39% Open Area)%

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL  $\pm 1/16$ "  
ANGULAR:  $\pm 5$  DEG.  
TWO PLACE DECIMAL  $\pm 0.03$   
THREE PLACE DECIMAL  $\pm 0.015$

EST WGT  
4.9 lbs.  
MATERIAL  
304 Stainless Steel  
FINISH  
Natural

Round Wire Mesh Basket: 10Dia. x 12H,  
304 SS, 3/16 Rod Frame, No Handles,  
Mesh: 8 x .047

SIZE **B** DWG. NO.  
TMT-100RND120-N08S

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS  
DRAWING IS THE SOLE PROPERTY OF  
THREE M TOOL. ANY REPRODUCTION IN  
PART OR AS A WHOLE WITHOUT THE  
WRITTEN PERMISSION OF THREE M TOOL  
IS PROHIBITED.

DO NOT SCALE DRAWING

SCALE: 1:5

SHEET 1 OF 1