


$\phi \frac{3}{16}$ "
Rod Frame



Lined Bottom and Sides with
30 Mesh x .012" Woven Wire
(.021" Openings, 40% Open Area)

UNLESS OTHERWISE SPECIFIED:

DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL $\pm 1/16$ "
ANGULAR: ± 5 DEG.
TWO PLACE DECIMAL ± 0.03
THREE PLACE DECIMAL ± 0.015

EST WGT	2.1 lbs.
MATERIAL	304 Stainless Steel
FINISH	Natural

DO NOT SCALE DRAWING

Round Wire Mesh Basket: 10Dia. x 12H,
304 SS, 3/16 Rod Frame, No Handles,
Mesh: 30 x .012

SIZE **B** DWG. NO.
TMT-100RND120-N30S

SCALE: 1:5

SHEET 1 OF 1

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
THREE M TOOL. ANY REPRODUCTION IN
PART OR AS A WHOLE WITHOUT THE
WRITTEN PERMISSION OF THREE M TOOL
IS PROHIBITED.