



Lined Bottom and Sides with
2 Mesh x .063" Welded Wire
(.437" Openings, 76% Open Area)

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL $\pm 1/16''$
ANGULAR: ± 5 DEG.
TWO PLACE DECIMAL ± 0.03
THREE PLACE DECIMAL ± 0.015

Rectangular Wire Mesh Basket:
12Lx6Wx3H, 304 SS, 1/4 Rod Frame,
Stacking Handles, Mesh: 2 x .063

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
THREE M TOOL. ANY REPRODUCTION IN
PART OR AS A WHOLE WITHOUT THE
WRITTEN PERMISSION OF THREE M TOOL
IS PROHIBITED.

EST WGT
2.9 lbs.
MATERIAL
304 Stainless Steel
FINISH
Natural
DO NOT SCALE DRAWING

SIZE **B** DWG. NO.
TMT-120060030-A02S

SCALE: 1:3

SHEET 1 OF 1