



Lined Bottom and Sides with  
4 Mesh x .063" Woven Wire  
(.187" Openings, 56% Open Area)

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL  $\pm 1/16"$   
ANGULAR:  $\pm 5$  DEG.  
TWO PLACE DECIMAL  $\pm 0.03$   
THREE PLACE DECIMAL  $\pm 0.015$

EST WGT  
4.1 lbs.  
MATERIAL  
304 Stainless Steel  
FINISH  
Natural

**Rectangular Wire Mesh Basket:**  
12Lx6Wx6H, 304 SS, 1/4 Rod Frame,  
No Handles, Mesh: 4 x .063

SIZE **B** DWG. NO.  
TMT-120060060-N04S

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS  
DRAWING IS THE SOLE PROPERTY OF  
THREE M TOOL. ANY REPRODUCTION IN  
PART OR AS A WHOLE WITHOUT THE  
WRITTEN PERMISSION OF THREE M TOOL  
IS PROHIBITED.

DO NOT SCALE DRAWING

SCALE: 1:3

SHEET 1 OF 1