



Lined Bottom and Sides with
8 Mesh x .047" Woven Wire
(.078" Openings, 39% Open Area)

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL $\pm 1/16"$
ANGULAR: ± 5 DEG.
TWO PLACE DECIMAL ± 0.03
THREE PLACE DECIMAL ± 0.015

EST WGT
4.4 lbs.
MATERIAL
304 Stainless Steel
FINISH
Natural

Rectangular Wire Mesh Basket:
12Lx6Wx6H, 304 SS, 1/4 Rod Frame,
No Handles, Mesh: 8 x .047

SIZE **B** DWG. NO.
TMT-120060060-N08S

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

DO NOT SCALE DRAWING

SCALE: 1:3

SHEET 1 OF 1