





8 7 6 5 4 3 2 1

D
C
B
A



Lined Bottom and Sides with
2 Mesh x .063" Welded Wire
(.437" Openings, 76% Open Area)

UNLESS OTHERWISE SPECIFIED:

DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL ± 1/16"
ANGULAR: ± 5 DEG.
TWO PLACE DECIMAL ±0.03
THREE PLACE DECIMAL ±0.015

EST WGT
5.0 lbs.

MATERIAL
304 Stainless Steel

FINISH
Natural

DO NOT SCALE DRAWING

Rectangular Wire Mesh Basket:
12Lx12Wx6H, 304 SS, 1/4 Rod Frame,
Stacking Handles, Mesh: 2 x .063

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

SIZE **B** DWG. NO. TMT-120120060-A02S

8 7 6 5 4 3 2 1