



Lined Bottom and Sides with 30 Mesh x .012" Woven Wire (.021" Openings, 40% Open Area)

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN INCHES
 TOLERANCES:
 FRACTIONAL ± 1/16"
 ANGULAR: ± 5 DEG.
 TWO PLACE DECIMAL ±0.03
 THREE PLACE DECIMAL ±0.015

EST WGT 4.4 lbs.
 MATERIAL 304 Stainless Steel
 FINISH Natural

Rectangular Wire Mesh Basket:
 12Lx12Wx6H, 304 SS, 1/4 Rod Frame,
 Stacking Handles, Mesh: 30 x .012

SIZE **B** DWG. NO. TMT-120120060-A30S

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.