





D  
C  
B  
A

D  
C  
B  
A



Lined Bottom and Sides with  
2 Mesh x .063" Welded Wire  
(.437" Openings, 76% Open Area)

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED:	
DIMENSIONS ARE IN INCHES	
TOLERANCES:	
FRACTIONAL	± 1/16"
ANGULAR	± 5 DEG.
TWO PLACE DECIMAL	±0.03
THREE PLACE DECIMAL	±0.015
EST WGT	6.0 lbs.
MATERIAL	304 Stainless Steel
FINISH	Natural
DO NOT SCALE DRAWING	

**Rectangular Wire Mesh Basket:**  
12Lx12Wx9H, 304 SS, 1/4 Rod Frame,  
Stacking Handles, Mesh: 2 x .063

SIZE **B** DWG. NO. TMT-120120090-A02S

SCALE: 1:5

SHEET 1 OF 1