



Lined Bottom and Sides with 4 Mesh x .063" Woven Wire (.187" Openings, 56% Open Area)

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN INCHES
 TOLERANCES:
 FRACTIONAL ± 1/16"
 ANGULAR: ± 5 DEG.
 TWO PLACE DECIMAL ±0.03
 THREE PLACE DECIMAL ±0.015

EST WGT 7.0 lbs.
 MATERIAL 304 Stainless Steel
 FINISH Natural

DO NOT SCALE DRAWING

Rectangular Wire Mesh Basket:
 12Lx12Wx12H, 304 SS, 1/4 Rod Frame,
 Stacking Handles, Mesh: 4 x .063

SIZE **B** DWG. NO. TMT-120120120-A04S

SCALE: 1:6

SHEET 1 OF 1

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.